

# Macro lens

## Componon 5.6/135-0017

For future tasks in industrial optics, the goal of Schneider-Kreuznach is to continue this tradition with modern, high-quality lenses in the field of digital applications. These lenses in their robust plastic housings are a good solution when using large linear and area sensors in a wide range of applications. A far-reaching and sophisticated optical design with constantly high manufacturing quality is a matter of course. The excellent optical coatings were designed especially for the glass types used. This ensures that the lens is optimally attuned to its application area. Flexible use due to the wide magnification range and the high optical quality with its logically limited starting aperture, low chromatic aberration and optimisation at small imaging distances all combine to make these lenses unique.

For the use with UNIFOC 58 / 76 a M50 x 0.75 to Leica Adapter is required (Code No. 17231)



Componon 5.6/135

### Key Features

- Excellent optical imaging performance for large sensors
- 100% quality control guarantees reliability and constant quality
- Low maintenance requirements, therefore high system reliability

### Applications

- Machine Vision and other imaging applications
- PCB inspection
- LCD inspection
- OLED inspection
- Solar inspection

### Technical Specifications

F-number	5.6
Focal length	135.7 mm
Image circle	150.0 mm
Magnification	0.5 – 0.04
Transmission	400 - 700 nm
Interface	M50 x 0,75
Weight	197 gr.
Filter Thread	M49 x 0.75
Code No.	39569



### Contact

Jos. Schneider Optische Werke GmbH  
 Ringstraße 132  
 55543 Bad Kreuznach  
 Germany  
 Phone +49 671 601-205  
 Fax +49 671 601-286  
[www.schneiderkreuznach.com](http://www.schneiderkreuznach.com)  
[industrie@schneiderkreuznach.com](mailto:industrie@schneiderkreuznach.com)

Schneider Optical Technologies Co., Ltd.  
 Rm. A505 Yingdali Science Park, Hongmian Rd.,  
 Futian Free Trade Zone, Shenzhen 518038,  
 P.R. China  
 Phone: +86 755 88 32 11 70  
 Fax: +86 755 88 32 11 75  
[www.schneiderkreuznach.com](http://www.schneiderkreuznach.com)  
[info@schneider-asiapacific.com](mailto:info@schneider-asiapacific.com)


Schneider Optics Inc.  
 285 Oser Ave.  
 Hauppauge, NY 11788  
 USA  
 Phone +1 631 761-5000  
 Fax +1 631 761-5090  
[www.schneideroptics.com/industrial](http://www.schneideroptics.com/industrial)  
[industrial@schneideroptics.com](mailto:industrial@schneideroptics.com)

# Componon 5.6/135



## COMPONON-S 5.6/135


$f' = 135.7 \text{ mm}$	$\beta_p' = 0.987$
$s_F = -109.2 \text{ mm}$	$s_{EP} = 28.4 \text{ mm}$
$s_F' = 112.7 \text{ mm}$	$s_{AP}' = -21.2 \text{ mm}$
$HH' = -3.0 \text{ mm}$	$\Sigma d = 46.6 \text{ mm}$



## RELATIVE ILLUMINATION

The relative illumination is shown for the given focal distances or magnifications.


	$f / 5.6$	$f / 8.0$	$f / 11.0$
—	$\beta' = -0.0833$	$u'_{max} = 75.6$	$00' = 1908.$
- -	$\beta' = -0.1667$	$u'_{max} = 75.5$	$00' = 1105.$
- - -	$\beta' = -0.3333$	$u'_{max} = 75.5$	$00' = 721.$



## DISTORTION

Distortion is shown for the given focal distances or magnifications. Positive values indicate pincushion distortion and negative values barrel distortion.

—	$\beta' = -0.0833$	$u'_{max} = 75.6$	$00' = 1908.$
- -	$\beta' = -0.1667$	$u'_{max} = 75.5$	$00' = 1105.$
- - -	$\beta' = -0.3333$	$u'_{max} = 75.5$	$00' = 721.$



## TRANSMITTANCE

Relative spectral transmittance is shown with reference to wavelength.


# Componon 5.6/135

## COMPONON-S 5.6/135


MODULATION with reference to the relative image height

Wavelength $\lambda$	[nm]	546	706	644	480	436	405
Spectral weighting	[%]	27.4	12.4	24.1	18.3	12.6	5.2
Spatial frequency R	[1/mm]	10	20	40			
Format	[mm X mm]	94.0	X118.0				
Diagonal $2u'$	[mm]	150.9					


radial —  
tangential - -



$f' = 135.7$   $f/5.6$   $1/\beta' = -12.00$   $00' = 1908$ .  $f' = 135.7$   $f/8.0$   $1/\beta' = -12.00$   $00' = 1908$ .  $f' = 135.7$   $f/11.0$   $1/\beta' = -12.00$   $00' = 1908$ .



$f' = 135.7$   $f/5.6$   $1/\beta' = -6.00$   $00' = 1105$ .  $f' = 135.7$   $f/8.0$   $1/\beta' = -6.00$   $00' = 1105$ .  $f' = 135.7$   $f/11.0$   $1/\beta' = -6.00$   $00' = 1105$ .



$f' = 135.7$   $f/5.6$   $1/\beta' = -3.00$   $00' = 721$ .  $f' = 135.7$   $f/8.0$   $1/\beta' = -3.00$   $00' = 721$ .  $f' = 135.7$   $f/11.0$   $1/\beta' = -3.00$   $00' = 721$ .

Focusing :  $MTF_{max}$  at  $f/5.6$  ,  $R = 20$  1/mm,  $u'/u'_{max} = 0$